

# RECTANGULAR TOWER LED

#### **Features**

- High intensity
- Wide viewing angle
- General purpose leads
- Reliable and rugged


Absolute Maximum Ratings at Ta=25℃

Parameter Parameter	Max.	Unit	
Power Dissipation	100	mW	
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA	
Continuous Forward Current	40	mA	
Derating Linear From 50°C	0.4	mA / °C	
Reverse Voltage	5	V	
Operating Temperature Range	-40°C to +80°C		
Storage Temperature Range	-40°C to +80°C		
Lead Soldering Temperature [4mm(.157") From Body]	260°C for 5 Seconds		

#### Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Protruded resin under flange is 1.0mm (.04") max.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

## **Package Dimensions**



Unit: mm (inches)

Tolerance: ± 0.25mm (.010") max.

Part No.	Emitted Color	Lens Color	Peak Wavelength λp (nm)	Vf (V) I <sub>f</sub> = 20mA (Note E1)	lv (mcd) (Note E2)	Viewing Angle 2 <i>θ</i> <sub>1/2</sub> (Deg) (Note E3)
				Min Typ	Min Typ	
EL-18R5U31	Hi-Red	Red Diffused	660	1.7 - 2.0	12 – 35	124
EL-18G5U31	Hi-Green	Green Diffused	570	1.7 - 2.2	6.0 – 15	124
EL-18Y5U31	Hi-Yellow	Yellow Diffused	590	1.7 - 2.0	15 – 25	124
EL-18O5U32	Hi-Red	Orange Diffused	610	1.7 - 2.0	18 – 30	124

### Parameter Test Condition

Luminous Intensity I<sub>f</sub> = 20mA (Note E1. Luminous intensity is measured with a light sensor and filter combination that approximates

the CIE eye-response curve.)

Dominant Wavelength  $I_f = 20$ mA (Note E2: The dominant wavelength ( $\lambda$ d) is derived from the CIE chromaticity diagram and represents

the single wavelength which defines the color of the device.)

Peak Emission Wavelength I<sub>f</sub> = 20mA

Viewing Angle (Note E3.  $\theta_{1/2}$  is the off-axis angle at which the luminous intensity is half the axial luminous intensity.)

 $\begin{array}{lll} \mbox{Spectral Line Half-Width} & \mbox{I}_{\mbox{f}} = 20\mbox{mA} \\ \mbox{Forward Voltage} & \mbox{I}_{\mbox{f}} = 20\mbox{mA} \\ \mbox{Reverse Current} & \mbox{I}_{\mbox{f}} = 20\mbox{mA} \\ \end{array}$