

# **ROUND-TOWER TYPE LED**

## **Features**

- High intensity
- Wide viewing angle
- General purpose leads
- Reliable and rugged


Absolute Maximum Ratings at Ta=25℃

Absolute maximum ratings at 1a 20 C								
Parameter	Max.	Unit						
Power Dissipation	100	mW						
Peak Forward Current	100	mA						
(1/10 Duty Cycle, 0.1ms Pulse Width)	100							
Continuous Forward Current	40	mA						
Derating Linear From 50°C	0.4	mA / °C						
Reverse Voltage	5	V						
Operating Temperature Range	-40°C to +80°C							
Storage Temperature Range	-40°C to +80°C							
Lead Soldering Temperature	260°C for 5 Seconds							
[4mm(.157") From Body]	200 C 101 5 Seconds							

#### Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Protruded resin under flange is 1.0mm (.04") max.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

## **Package Dimensions**



Unit: mm (inches)

Tolerance: ± 0.25mm (.010") max.

Part No.	Emitting Color	Lens Color	Peak Wavelength λp (nm)	Vf (V) I <sub>f</sub> = 20mA (Note E1)		lv (n (Note	•	Viewing Angle 2θ <sub>1/2</sub> (Deg) (Note E3)
				Min	Тур	Min	Тур	
EL-2R62U31	Hi-Red	Red Diffused	660	1.7 -	2.0	30 -	- 50	100
EL-2G62U31	Hi-Green	Green Diffused	570	1.7 -	2.2	18 -	- 35	100
EL-2Y62U31	Hi-Yellow	Yellow Diffused	590	1.7 -	2.0	20 -	- 35	100
EL-2O62U31	Hi-Orange	Orange Diffused	610	1.7 -	2.2	25 -	- 45	100

### Parameter Test Condition

 $Luminous\ Intensity \\ I_f = 20mA\ (Note\ E1.\ Luminous\ intensity\ is\ measured\ with\ a\ light\ sensor\ and\ filter\ combination\ that\ approximates$ 

the CIE eye-response curve.)

Dominant Wavelength  $I_f = 20mA$  (Note E2: The dominant wavelength ( $\lambda d$ ) is derived from the CIE chromaticity diagram and represents

the single wavelength which defines the color of the device.)

Peak Emission Wavelength  $I_f = 20 \text{mA}$ 

Viewing Angle (Note E3.  $\theta_{1/2}$  is the off-axis angle at which the luminous intensity is half the axial luminous intensity.)

 $\begin{array}{lll} \mbox{Spectral Line Half-Width} & \mbox{I}_{\mbox{f}} = 20\mbox{mA} \\ \mbox{Forward Voltage} & \mbox{I}_{\mbox{f}} = 20\mbox{mA} \\ \mbox{Reverse Current} & \mbox{I}_{\mbox{f}} = 20\mbox{mA} \\ \end{array}$