

## **Features**

- High intensity
- Wide viewing angle
- General purpose leads
- Reliable and rugged


Absolute Maximum Ratings at Ta=25

Absolute Maximum Natings at Ta=25							
Parameter Max.		Unit					
Power Dissipation	100	mW					
Peak Forward Current	100	mA					
(1/10 Duty Cycle, 0.1ms Pulse Width)	100						
Continuous Forward Current	40	mA					
Derating Linear From 50	0.4	mA /					
Reverse Voltage	5	V					
Operating Temperature Range	-40 to +80						
Storage Temperature Range	-40 to +80						
Lead Soldering Temperature	260 for 5 Seconds						
[4mm(.157") From Body]	260 for 5 Seconds						

## Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Protruded resin under flange is 1.0mm (.04") max.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

## **Package Dimensions**



Unit: mm (inches)

Tolerance: ±0.25mm (.010") max

Part No.	Emitted Color	Lens Color	Peak Wavelength λp (nm)	Vf (V) I <sub>f</sub> = 20mA (Note E1)	Iv (mcd) (Note E2)	Viewing Angle 2θ <sub>1/2</sub> (Deg) (Note E3)
				Min Typ	Min Typ	
EL-8R631	Red	Red Diffused	660	1.6 – 1.8	2.5 – 30	60
EL-8G631	Green	Green Diffused	568	1.7 – 2.2	2.5 – 10	60
EL-8Y631	Yellow	Yellow Diffused	590	1.6 – 2.1	2.5 – 10	60
EL-8R232	Red	Water Clear	660	1.6 – 1.8	6.0 – 30	25
EL-8G232	Green	Water Clear	568	1.7 – 2.2	6.0 – 30	25
EL-8Y232	Yellow	Water Clear	590	1.6 – 2.1	6.0 – 30	25
EL-8R233	Red	Red Transparent	660	1.6 – 1.8	6.0 – 30	25
EL-8G233	Green	Green Transparent	568	1.7 – 2.2	6.0 – 30	25
EL-8Y233	Yellow	Yellow Transparent	590	2.0 – 2.6	6.0 – 30	25

Parameter Test Condition

Luminous Intensity I<sub>f</sub> = 20mA (Note E1. Luminous intensity is measured with a light sensor and filter combination that approximates

the CIE eye-response curve.)

 $\label{eq:local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_local_$ 

the single wavelength which defines the color of the device.)

Peak Emission Wavelength  $I_f = 20 \text{mA}$ 

Viewing Angle (Note E3. 1/2 is the off-axis angle at which the luminous intensity is half the axial luminous intensity.)

 $\label{eq:spectral Line Half-Width} \begin{aligned} & \text{Spectral Line Half-Width} & & \text{I}_{\text{f}} = 20\text{mA} \\ & \text{Forward Voltage} & & & \text{I}_{\text{f}} = 20\text{mA} \\ & \text{Reverse Current} & & & \text{I}_{\text{f}} = 20\text{mA} \end{aligned}$